



K7G10M15P

16A Link Lead 10m 1.5mm 4 Core Plug to Plug

Technical Features

Architecture

Number of poles	4
-----------------	---

Voltage

Max. operating voltage	240 V
------------------------	-------

Electric current

Rated current	16 A
---------------	------

Cable

Cable diameter	10 mm
----------------	-------

Connection

Conductor cross-section	1.50 - 1.50 mm ²
-------------------------	-----------------------------

Equipment

Mechanical coding	Yes
Type cable side 1	Plug
Type cable side 2	Plug
Type of cable	Connecting cable

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

Materials

Colour	White
--------	-------

Cable

Cable permanent temperature resistant to	90 °C
--	-------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes