



P64AXR/LSF/2.0

P64AXR c/w 4 Core 0.75mm² 2m LS0H Lead

Technical Features

Architecture

Number of poles	4
-----------------	---

Voltage

Max. operating voltage	240 V
------------------------	-------

Electric current

Rated current	6 A
---------------	-----

Cable

Cable diameter	7 mm
----------------	------

Cable length	2 m
--------------	-----

Dimensions

Length	2000 mm
--------	---------

Connection

Conductor cross-section	0.75 - 0.75 mm ²
-------------------------	-----------------------------

Equipment

Mechanical coding	Yes
-------------------	-----

Type cable side 1	Plug
-------------------	------

Type cable side 2	Free conductor end
-------------------	--------------------

Type of cable	Device connection cable
---------------	-------------------------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

Materials

Colour	Red
--------	-----

Cable

Cable permanent temperature resistant to	90 °C
--	-------

Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----