



WMGSDP2B\_TD

**20A 1 Way Double Pole Switch Marked 'TUMBLE DRYER' Black**

**Technical Features**

**Electric current**

|                   |      |
|-------------------|------|
| Switching current | 20 A |
|-------------------|------|

**Installation, mounting**

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Materials**

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

|                |        |
|----------------|--------|
| Surface finish | Glossy |
|----------------|--------|

|          |                   |
|----------|-------------------|
| Material | Urea formaldehyde |
|----------|-------------------|

|           |           |
|-----------|-----------|
| Treatment | Untreated |
|-----------|-----------|

**Identification**

|                      |  |
|----------------------|--|
| Assembly arrangement | Basic element with central cover plate |
|----------------------|--|

**Connectivity**

|               |                  |
|---------------|------------------|
| Mounting type | Snap-on mounting |
|---------------|------------------|

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

**Dimensions**

|            |            |
|------------|------------|
| Dimensions | 59 x 25 mm |
|------------|------------|

|                |          |
|----------------|----------|
| Built-in depth | 13.10 mm |
|----------------|----------|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Architecture**

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

**Texts**

|          |  |
|----------|--|
| Lighting | Without lighting (cannot be illuminated) |
|----------|--|

|             |        |
|-------------|--------|
| Switch mode | 2-pole |
|-------------|--------|

**Sustainability**

|              |     |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|