



K7P1M1W

#### 10A Luminaire lead 1.5m 1mm 5 core Plug to Wire

##### Technical Features

###### Architecture

Number of poles	5
-----------------	---

###### Voltage

Max. operating voltage	240 V
------------------------	-------

###### Electric current

Rated current	10 A
---------------	------

###### Cable

Cable diameter	10 mm
----------------	-------

###### Connection

Conductor cross-section	1 - 1 mm <sup>2</sup>
-------------------------	-----------------------

###### Equipment

Mechanical coding	Yes
-------------------	-----

Type cable side 1	Plug
-------------------	------

Type cable side 2	Free conductor end
-------------------	--------------------

Type of cable	Device connection cable
---------------	-------------------------

###### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

###### Materials

Colour	White
--------	-------

###### Cable

Cable permanent temperature resistant to	90 °C
--	-------

###### Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----