



P64AXI1.0LSFI4

P64AX c/w 4 Core 1.00mm² 4m LS0H Lead

Technical Features

Architecture

|                 |   |
|-----------------|---|
| Number of poles | 4 |
|-----------------|---|

Voltage

|                        |       |
|------------------------|-------|
| Max. operating voltage | 240 V |
|------------------------|-------|

Electric current

|               |     |
|---------------|-----|
| Rated current | 6 A |
|---------------|-----|

Cable

|                |      |
|----------------|------|
| Cable diameter | 8 mm |
| Cable length   | 4 m  |

Dimensions

|        |         |
|--------|---------|
| Length | 1000 mm |
|--------|---------|

Connection

|                         |           |
|-------------------------|-----------|
| Conductor cross-section | 1 - 1 mm² |
|-------------------------|-----------|

Equipment

|                   |                         |
|-------------------|-------------------------|
| Mechanical coding | Yes                     |
| Type cable side 1 | Plug                    |
| Type cable side 2 | Free conductor end      |
| Type of cable     | Device connection cable |

Use conditions

|                                                          |   |
|----------------------------------------------------------|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
|----------------------------------------------------------|---|

Materials

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

Cable

|                                          |       |
|------------------------------------------|-------|
| Cable permanent temperature resistant to | 90 °C |
|------------------------------------------|-------|

Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |