



WMSSU83FON!FRE

### 13A FCU Switched with LED Indicator and Flex Outlet Marked FREEZER

#### Technical Features

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

##### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Dimensions

Dimensions	86 x 86 mm
Built-in depth	25.30 mm

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Electric current

Rated current	13 A
---------------	------

##### Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	With control LED for ON
Switch mode	2-pole

##### Sustainability

RoHS conform	Yes
--------------	-----