



WMSSU83FON!FRE

**13A FCU Switched with LED Indicator and Flex Outlet Marked FREEZER**

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Materials**

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

**Identification**

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	86 x 86 mm
Built-in depth	25.30 mm

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Electric current**

Rated current	13 A
---------------	------

**Texts**

Installation mode	For flush-mounted and hollow wall mounting
Lighting	With control LED for ON
Switch mode	2-pole

**Sustainability**

RoHS conform	Yes
--------------	-----