



PCR2000LSF!2.0

**PCR2000 c/w 3 Core 0.75mm<sup>2</sup> 2m LSOH Lead**

**Technical Features**

**Architecture**

Number of poles	3
-----------------	---

**Voltage**

Max. operating voltage	240 V
------------------------	-------

**Electric current**

Rated current	6 A
---------------	-----

**Cable**

Cable diameter	7 mm
----------------	------

Cable length	2 m
--------------	-----

**Dimensions**

Length	2000 mm
--------	---------

**Connection**

Conductor cross-section	0.75 - 0.75 mm <sup>2</sup>
-------------------------	-----------------------------

**Equipment**

Mechanical coding	Yes
-------------------	-----

Type cable side 1	Plug
-------------------	------

Type cable side 2	Free conductor end
-------------------	--------------------

Type of cable	Device connection cable
---------------	-------------------------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

**Materials**

Colour	White
--------	-------

**Cable**

Cable permanent temperature resistant to	90 °C
--	-------

**Sustainability**

RoHS conform	Yes
--------------	-----