



HXA027H

**Alarm contact NO-NC right side (x630/P630)**

**Technical Features**

**Electric current**

Rated current	3 A
Rated current 230 V AC15	3 A

**Connectivity**

Type of connection	quickconnect
Mounting type	Click mounting

**Connection**

Type of contacts	1x changeover
Cross-section flexible conductor	0.5 - 1.25 mm <sup>2</sup>
Cross-section rigid conductor	0.5 - 1.25 mm <sup>2</sup>

**Voltage**

Rated impulse withstand voltage Uimp	1500 V
Type voltage supply	AC/DC

**Power**

Total power loss under IN	3 W
---------------------------	-----

**Equipment**

Number of INV contacts	0
Number of NC contacts	1

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------