



K7A10M15P

### 16A Luminaire Lead 10m 1.5mm 3 Core Plug to Plug

#### Technical Features

##### Architecture

Number of poles	3
-----------------	---

##### Voltage

Max. operating voltage	240 V
------------------------	-------

##### Electric current

Rated current	16 A
---------------	------

##### Cable

Cable diameter	9 mm
----------------	------

##### Connection

Conductor cross-section	1.50 - 1.50 mm <sup>2</sup>
-------------------------	-----------------------------

##### Equipment

Mechanical coding	Yes
Type cable side 1	Plug
Type cable side 2	Plug
Type of cable	Connecting cable

##### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

##### Materials

Colour	White
--------	-------

##### Cable

Cable permanent temperature resistant to	90 °C
--	-------

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes