



6765832045

Soc.out. earth.pin+hinged cover,enhncd contact prot.,screw-in lift ,R.1.3,bl.

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Black
RAL code	9005
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	71 mm
Width	71 mm
Depth	48.90 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	31.30 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

**Equipment**

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
---------------------	----

**Cover, door**

Type of lid	Self-closing hinged cover
-------------	---------------------------

**Capacity**

Number of modules	1
-------------------	---

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

---

**Texts**

Imprint	With imprint
Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

---

**Suitable for**

R.x

---

**Sustainability**

Halogen free	Yes
RoHS conform	Yes