



6765832089

Soc.out. earth.pin+hinged cover,enhncd contact prot.,screw-in lift term.,R1.3,wh

#### Technical Features

##### Voltage

Rated voltage 250 V

##### Electric current

Rated current 16 A

##### Frequency

Frequency 50 - 60 Hz

##### Materials

Colour Polar white

RAL code 9010

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

##### Dimensions

Height 71 mm

Width 71 mm

Depth 48.90 mm

Number of units 1

Built-in depth flush-mounted boxes 31 mm

Built-in depth 31.30 mm

##### Installation, mounting

Mounting on Flush mounting

##### Connectivity

Type of connection Screw terminal

Mounting type Screw mounting  
Claw mounting

##### Equipment

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid Yes

With round protective earth pin Yes

With signal lamp No

With lock No

##### Accessories

Has labelling field No

##### Cover, door

Type of lid Self-closing hinged cover

##### Capacity

Number of modules 1

##### Safety

With enhanced contact protection Yes

Impact resistance IK IK05

Ingress Protection (IP) class IP20

##### Functions

With orientation lighting No

With function lighting No

---

**Texts**

|                    |                              |
|--------------------|------------------------------|
| Imprint            | With imprint                 |
| Cover              | Central cover plate          |
| Protection         | Enhanced contact protection  |
| Type of connection | With screw-in lift terminals |

---

**Suitable for**

R.x

---

**Sustainability**

|              |     |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |