




EHN171



Weekly time switch 1 channel, 3 modules with reserve

Technical Features

Equipment

Number of channels	1
--------------------	---

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Power consumption during operation	0.50 W
230 V incandescent and halogen lamp	1100 W
Power incandescent lamp	900 - 900 W

Functions

Number of function channels	1
-----------------------------	---

Connection

Number of contacts	1
Cross-section flexible conductor	0.5 - 6 mm ²
Cross-section rigid conductor	0.5 - 6 mm ²

Use conditions

Operating temperature	-10 - +55 °C
-----------------------	--------------

Capacity

Number of modules	3
-------------------	---

Dimensions

Height	90 mm
Width	54 mm
Depth	60 mm

Texts

Switch mode	Change-over contact
Installation mode	For mounting on DIN rail

Electric current

Max. power (cos phi 0,6)	4 A
--------------------------	-----

Endurance

Electrical durability at nominal load in AC1 in operating cycles	50000
--	-------

Texts

Type of connection	With screw terminals
--------------------	----------------------

Voltage

Rated operational voltage Ue	230 - 240 V
------------------------------	-------------

Power

Power loss at full load	1 W
-------------------------	-----

Settings

Programme cycles	Programme cycles: 1 x 7 days
Shortest switching time	2 h

Lighting

LED lamp power	180 W
----------------	-------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes