




EHN010



**Daily time switch 1 channel, 1 module**

**Technical Features**

**Equipment**

Number of channels	1
--------------------	---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Power**

Power consumption during operation	1 W
230 V incandescent and halogen lamp	900 W
Power incandescent lamp	1000 - 1000 W

**Functions**

Number of function channels	1
-----------------------------	---

**Connection**

Number of contacts	1
Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1 - 6 mm <sup>2</sup>

**Use conditions**

Operating temperature	-20 - +50 °C
-----------------------	--------------

**Capacity**

Number of modules	1
-------------------	---

**Dimensions**

Height	90 mm
Width	17.5 mm
Depth	60 mm

**Texts**

Switch mode	NO contact
Installation mode	For mounting on DIN rail

**Electric current**

Max. power (cos phi 0,6)	3 A
--------------------------	-----

**Endurance**

Electrical durability at nominal load in AC1 in operating cycles	50000
--	-------

**Texts**

Type of connection	With screw terminals
--------------------	----------------------

**Voltage**

Rated operational voltage Ue	230 - 240 V
------------------------------	-------------

**Power**

Power loss at full load	1 W
-------------------------	-----

**Settings**

Programme cycles	Programme cycle: 24 hours
Shortest switching time	15 min

**Lighting**

LED lamp power	300 W
----------------	-------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes