



75242060



**KNX Movement detector module comfort 1,10m (integrated bus coupling unit)**

**Technical Features**

**Dimensions**

Installation height	1.10 - 1.10 m
Recommended installation height	1.10 - 1.10 m

**Settings**

Supported configuration mode	ETS
Minimal duty cycle	10 s

**Functions**

Maximal duty cycle	30 min
--------------------	--------

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Voltage**

Operating voltage over bus	21 - 32 V
----------------------------	-----------

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Lighting**

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

**Detection**

Detection angle adjustable	45 - 90 °
Detection angle horizontal	0 - 180

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Materials**

Material	Metal Plastic
----------	------------------

**Texts**

Push button	Integrated button for manual control of bus functions can be configured With button for automatic/permanent ON/ON for 2 hours/permanent OFF
Operating mode	Operating modes: Automatic, permanent ON, ON for 2 hours, permanent OFF
Function	Push-button function: Switching functions, dimming functions, blind control functions, value transmitter functions, forced control functions, scene functions Specification of the controller operating mode
Installation mode	With dismantling protection