



75242060



#### KNX Movement detector module comfort 1,10m (integrated bus coupling unit)

##### Technical Features

##### Dimensions

Installation height	1.10 - 1.10 m
Recommended installation height	1.10 - 1.10 m

##### Settings

Supported configuration mode	ETS
Minimal duty cycle	10 s

##### Functions

Maximal duty cycle	30 min
--------------------	--------

##### Connectivity

With bus system KNX radio	No
---------------------------	----

##### Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

##### Scope of delivery

Bus connection included	Yes
-------------------------	-----

##### Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

##### Detection

Detection angle adjustable	45 - 90 °
Detection angle horizontal	0 - 180

##### Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

##### Materials

Material	Metal Plastic
----------	------------------

##### Texts

Push button	Integrated button for manual control of bus functions can be configured With button for automatic/permanent ON/ON for 2 hours/permanent OFF
Operating mode	Operating modes: Automatic, permanent ON, ON for 2 hours, permanent OFF
Function	Push-button function: Switching functions, dimming functions, blind control functions, value transmitter functions, forced control functions, scene functions Specification of the controller operating mode
Installation mode	With dismantling protection