



75710004

IP-Control

Technical Features

Equipment

Web server	Yes
------------	-----

Voltage

Operating voltage	30 - 30 V
Type voltage supply	DC

Connectivity

Type of interface bus system/media gateway	LAN-systems interface
--	-----------------------

Settings

Supported configuration mode	ETS
------------------------------	-----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	0 - 35 °C
-----------------------	-----------

Controls and indicators

With LED indication	Yes
---------------------	-----

Dimensions

Width	144 mm
Dimensions	90 x 144 mm
Depth	64.50 mm
Number of width units	8

Connection

Connector/plug type	DRA (DIN-rail Adapter)
---------------------	------------------------

Texts

Encoding	Administration of 50 users for the control of access authorisation
Voltage	Operation with non-choked output of KNX voltage supply possible (pay attention to current consumption)
Type of connection	With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes