



289610

1-10 V push-button rot. potentiometer, NO contact, soft-lock, light control

Technical Features

Electric current

Momentary contact current 2 A

Frequency

Frequency 50 - 60 Hz

Architecture

Control/operation element Push & rotative switch

Materials

Transparent No

Dimensions

Height 71 mm

Width 71 mm

Depth 50 mm

Installation, mounting

Mounting on Flush mounting

Texts

Lighting E.g. for fluorescent lamps and LV halogen lamps

Type of connection With screw terminals

Sustainability

REACH-SVHC free Yes

RoHS conform Yes