



289610

1-10 V push-button rot. potentiometer, NO contact, soft-lock, light control

Technical Features

Electric current

Momentary contact current	2 A
---------------------------	-----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Push & rotative switch
---------------------------	------------------------

Materials

Transparent	No
-------------	----

Dimensions

Height	71 mm
Width	71 mm
Depth	50 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Texts

Lighting	E.g. for fluorescent lamps and LV halogen lamps
Type of connection	With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes