



28829909

Technical Features

Resistance

Impedance 4 Ω

Frequency

Frequency 170 - 18000 Hz

Dimensions

Built-in depth 35 mm

Materials

Colour Polar white

Surface finish Matt

Power

Music power handling 4 W

Texts

Installation mode Without spreader claws