



28829909

Technical Features

<b>Resistance</b>	
Impedance	4 $\Omega$
<b>Frequency</b>	
Frequency	170 - 18000 Hz
<b>Dimensions</b>	
Built-in depth	35 mm
<b>Materials</b>	
Colour	Polar white
Surface finish	Matt
<b>Power</b>	
Music power handling	4 W
<b>Texts</b>	
Installation mode	Without spreader claws