



28827003

Technical Features

Resistance

Impedance 8 Ω

Frequency

Frequency 170 - 18000 Hz

Dimensions

Built-in depth 35 mm

Materials

Colour Aluminium

Surface finish Matt

Material Aluminium

Treatment Varnished

Power

Music power handling 4 W

Texts

Installation mode Without spreader claws