



47548989

Double SCHUKO soc. out. cover plate, S.1, p. white glossy

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Duroplastic
Treatment	Untreated

Dimensions

Height	121.50 mm
Width	80.50 mm
Built-in depth flush-mounted boxes	31 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Mounting type	Claw mounting
---------------	---------------

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Cover, door

Type of lid	Without lid
-------------	-------------

Capacity

Number of modules	2
-------------------	---

Safety

Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Full cover plate
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

Product Datasheet

47548989

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes