



28846084

Radio Touch, Q.1/Q.3/Q.7, alu velvety, lacquered

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 60 Hz
Radio reception frequency	87.5 - 108.0 MHz

Materials

Colour	Aluminium
RAL code	9006
Surface finish	Velvety
Treatment	Varnished

Dimensions

Height	70.80 mm
Width	70.80 mm
Depth	46.50 mm
Built-in depth	33 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Connection

Cross-section loudspeaker	1.50 - 1.50 mm ²
Conductor cross-section	2.50 - 2.50 mm ²

Functions

Integrated DCF clock	Yes
----------------------	-----

Equipment

Type of display	Digital
-----------------	---------

Texts

Type of connection	With screw terminals
Junction	With 2 loudspeaker connections
Installation mode	For screw fastening
Function	Alarm clock with snooze function Sleep timer Countdown Volume control
Extension unit input	Extension unit input for separate on/off switching