



2902

**BLC universal touch dimmer LV house electronics**

**Technical Features**

**Voltage**

Operating voltage	230 - 230 V
-------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Material	Metal Plastic
----------	------------------

**Dimensions**

Built-in depth	22 mm
Height	71 mm
Width	71 mm
Depth	29.60 mm

**Architecture**

Control/operation element	Single push button
---------------------------	--------------------

**Use conditions**

Operating temperature	-20 - 45 °C
-----------------------	-------------

**Texts**

Dimming principle	Phase cut-on or cut-off according to load type, self-learning
Fuse	Short-circuit and overload-proof (electronic fuse)
Installation mode	With spreader claws
Type of connection	With screw terminals
Extension unit input	With extension unit input for BLC extension unit, BLC controller extension unit for motion detector and push-button, NO contact

**Equipment**

Substation input	Yes
------------------	-----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes