



2906



BLC relay switch insert house electronics

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

230 V incandescent and halogen lamp	2300 W
Fluorescent lamps in duo circuit	2300 W

Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

Dimensions

Built-in depth	22 mm
----------------	-------

Texts

Extension unit input	With extension unit input for BLC extension unit, BLC controller extension unit for motion detector and push-button, NO contact
Installation mode	With spreader claws
Type of connection	With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes