



386101

3-step switches, HVAC control

Technical Features

Voltage

Nominal voltage	250 - 250 V
Rated voltage	250 V

Electric current

Switching current	16 A
-------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Electric current

Rated current	16 A
---------------	------

Dimensions

Dimensions	71 x 71 mm
Depth	46 mm

Materials

Material	Metal Plastic
----------	------------------

Architecture

Control/operation element	Rotative
---------------------------	----------

Texts

Switch mode	Without neutral position: 2-1-3
Type of connection	With screw terminals