



2995

Motion detector compact 1.1 m (2-conductor)

Technical Features

Detection

Detection angle	180 - 180
Type of sensor	Movement detector

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Width	70.90 mm
Built-in depth	32 mm

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Colour	Polar white
Material	Metal Plastic

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Texts

Function	With switch-off pre-warning (can be deactivated) Not suitable for the installation of stair light switches Can only be used as individual unit
----------	--