



2996

Motion detector compact with relay switching contact 1.1 m (3-conductor)

Technical Features

Detection

Detection angle	180 - 180
Type of sensor	Movement detector

Settings

Minimal duty cycle	180 s
--------------------	-------

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Settings

Response brightness adjustable	Yes
Response sensitivity adjustable	Yes

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Width	70.90 mm
Built-in depth	32 mm
Installation height	1.10 - 1.10 m

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Colour	Polar white
Material	Metal Plastic

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Texts

Function	With switch-off pre-warning (can be deactivated) Not suitable for the installation of stair light switches Can only be used as individual unit
----------	--

Reach distance

Max. transmission range frontally	10 m
Max. transmission range sideways	6 m