



47537009

Double SCHUKO soc. out. cover plate, K.1, p. white glossy

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

Dimensions

Height 120.80 mm

Width 79.80 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Mounting type Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

Accessories

Has labelling field No

Capacity

Number of modules 2

Safety

Impact resistance IK IK05

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Full cover plate

Protection Without enhanced contact protection

Type of connection With plug-in terminals

Sustainability

REACH-SVHC free Yes