



474005

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 50 Hz

Materials

Colour Light grey

RAL code 7035

Surface finish Glossy
Matt

Material Thermoplastic

Treatment Untreated

Dimensions

Height 81 mm

Depth 58.50 mm

Installation, mounting

Mounting on Surface mounting

Connectivity

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid Yes

With round protective earth pin No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

Impact resistance IK IK05

Ingress Protection (IP) class IP44

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Complete housing

Protection Without enhanced contact protection

Type of connection With plug-in terminals

Terminal Wago clip-in 3-wire connection terminal for wiring