



474005

#### Technical Features

##### Electric current

Rated current	16 A
---------------	------

##### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Materials

Colour	Light grey
RAL code	7035
Surface finish	Glossy Matt
Material	Thermoplastic
Treatment	Untreated

##### Dimensions

Height	81 mm
Depth	58.50 mm

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	1
-------------------	---

##### Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP44

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Complete housing
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals