



47549909

Double SCHUKO soc. out. cover plate, S.1, p. white, matt, plastic

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

**Dimensions**

Height 121.50 mm

Width 80.50 mm

Built-in depth flush-mounted boxes 31 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Mounting type Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

**Accessories**

Has labelling field No

**Cover, door**

Type of lid Without lid

**Capacity**

Number of modules 2

**Safety**

Impact resistance IK IK05

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting No

**Identification**

With imprint No

**Texts**

Cover Full cover plate

Protection Without enhanced contact protection

Type of connection With plug-in terminals

**Sustainability**

REACH-SVHC free Yes