



478405



#### Technical Features

##### Voltage

Rated voltage	250 V
---------------	-------

##### Electric current

Rated current	16 A
---------------	------

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Materials

Colour	Light grey
--------	------------

RAL code	7035
----------	------

Surface finish	Glossy Matt
----------------	-------------

##### Material

Material	Thermoplastic
----------	---------------

##### Treatment

Treatment	Untreated
-----------	-----------

Dimensions	
------------	--

Height	75.10 mm
--------	----------

Depth	58.50 mm
-------	----------

##### Connection

Conductor cross-section	1.0 - 2.5 mm <sup>2</sup>
-------------------------	---------------------------

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Equipment

Connector/plug type socket outlet	SCHUKO
-----------------------------------	--------

Rotated central insert	No
------------------------	----

With hinged lid	Yes
-----------------	-----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	2
-------------------	---

##### Safety

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP44
-------------------------------	------

##### Functions

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

##### Texts

Imprint	Without imprint
---------	-----------------

Cover	Complete housing
-------	------------------

Wiring	Inserts wired-through
--------	-----------------------

Protection	Without enhanced contact protection
------------	-------------------------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Terminal	Wago clip-in 3-wire connection terminal for wiring
----------	--