



507105

### Technical Features

#### Electric current

Momentary contact current	10 A
---------------------------	------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	Light grey
Surface finish	Glossy Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No

#### Dimensions

Height	75 mm
Width	75 mm
Depth	52.30 mm

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	Yes

#### Safety

Ingress Protection (IP) class	IP44
-------------------------------	------

#### Accessories

Has labelling field	No
---------------------	----

#### Texts

Installation mode	For screw fastening
Lighting	Can be illuminated using neon and glow lamp unit with N-terminal For lighting and monitoring circuit
Terminal	Wago clip-in 3-wire connection terminal for wiring
Type of connection	With plug-in terminals