



EUM200



Voltage and phase control relay 1P+N/3P(N) 2 Change over contacts

Technical Features

Capacity

Number of modules	2
-------------------	---

Use conditions

Operating temperature	-25 - 55 °C
Storage/transport temperature	-25 - 70 °C

Connection

Cross-section flexible conductor	1.5 - 2.5 mm ²
Cross-section rigid conductor	2.5 - 4 mm ²

Power supply

Supply voltage	3N, 400/230 V
----------------	---------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Tripping

Max. permitted off-delay time	30 s
-------------------------------	------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Power

Total power loss under IN	1.20 W
---------------------------	--------

Dimensions

Height	87 mm
Width	35 mm
Depth	65 mm

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes