



75311008



Technical Features

Voltage

Operating voltage over bus	21 - 32 V
Auxiliary tension	230 - 230 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Equipment

Number of outputs	1
-------------------	---

Capacity

Number of modules	4
-------------------	---

Power

Power of variator	20 - 500 W
-------------------	------------

Connectivity

With bus system KNX radio	No
---------------------------	----

Settings

Supported configuration mode	ETS
------------------------------	-----

Texts

Fuse	Short-circuit and overload-proof (electronic fuse)
Dimming principle	Operating with LED and energy-saving lamps according to appropriate ETS configuration Phase cut-on or cut-off according to load type, self-learning
Function	Operating hours meter as forward or backward counter per channel Stairway function with switch-off warning according to DIN 18015-2
Type of connection	With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes