



75261159



KNX cont. 1.1 m, KNX - S.1, p. white glossy

Technical Features

Dimensions

Installation height	1.10 - 1.10 m
Recommended installation height	1.10 - 1.10 m

Settings

Supported configuration mode	ETS
Minimal duty cycle	0.13 s

Functions

Maximal duty cycle	9120 min
--------------------	----------

Connectivity

With bus system KNX radio	No
---------------------------	----

Scope of delivery

Bus connection included	No
-------------------------	----

Detection

Detection angle	180 - 180
Detection angle horizontal	0 - 180

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Material	Thermoplastic
----------	---------------

Texts

Function	Parameter definable lock function
----------	-----------------------------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes