



EUU100



Undervoltage control relay 1P+N/3P+N 1 Change over contact

Technical Features

Capacity

Number of modules	1
-------------------	---

Use conditions

Operating temperature	-25 - 55 °C
Storage/transport temperature	-25 - 70 °C

Connection

Cross-section flexible conductor	1.5 - 2.5 mm ²
Cross-section rigid conductor	2.5 - 4 mm ²

Power supply

Supply voltage	3N, 400/230 V
----------------	---------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Tripping

Max. permitted off-delay time	0.20 s
-------------------------------	--------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Power

Total power loss under IN	0.60 W
---------------------------	--------

Dimensions

Height	87 mm
Width	17.50 mm
Depth	65 mm

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes