



4283

**SCHUKO soc.out. surf.-mtd,bayonet hinged cover,enhncd contact prot.,screw , IP66**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 50 Hz

**Materials**

Colour Grey

RAL code 7011

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

**Dimensions**

Height 87.50 mm

Width 75 mm

**Installation, mounting**

Mounting on Surface mounting

**Connectivity**

Type of connection Screw terminal

Mounting type Screw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid Yes

With round protective earth pin No

**Accessories**

Has labelling field No

**Cover, door**

Type of lid Self-closing hinged cover

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection Yes

Impact resistance IK IK05

Ingress Protection (IP) class IP66

**Functions**

With orientation lighting No

With function lighting No

**Identification**

With imprint No

**Texts**

Cover Complete housing

Protection Enhanced contact protection

Type of connection With screw terminals