



4283

**SCHUKO soc.out. surf.-mtd,bayonet hinged cover,enhncd contact prot.,screw , IP66**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	Grey
RAL code	7011
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	87.50 mm
Width	75 mm

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No

**Accessories**

Has labelling field	No
---------------------	----

**Cover, door**

Type of lid	Self-closing hinged cover
-------------	---------------------------

**Capacity**

Number of modules	1
-------------------	---

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66

**Functions**

With orientation lighting	No
With function lighting	No

**Texts**

Imprint	Without imprint
Cover	Complete housing
Protection	Enhanced contact protection
Type of connection	With screw terminals