



387700

Rot. switch, intermediate, 1930/glass/R.classic

Technical Features

<b>Electric current</b>	
Switching current	10 A

<b>Installation, mounting</b>	
Mounting on	Flush mounting

<b>Voltage</b>	
Rated voltage	250 V

<b>Materials</b>	
Material	Duroplastic

<b>Identification</b>	
Assembly arrangement	Basic element

<b>Connectivity</b>	
Mounting type	Claw mounting

<b>Dimensions</b>	
Dimensions	71 x 71 mm
Built-in depth	32 mm

<b>Safety</b>	
Ingress Protection (IP) class	IP20

<b>Architecture</b>	
Control/operation element	Short rotary handle

<b>Electric current</b>	
Rated current	10 A

<b>Texts</b>	
Installation mode	With spreader claws
Type of connection	With screw terminals
Lighting	Without neon lamp
Switch mode	Intermediate