



507605



Technical Features

Electric current

Momentary contact current

10 A

Voltage

Rated voltage

250 V

Materials

Colour

Light grey

Surface finish

Glossy

Matt

Material

Thermoplastic

Treatment

Untreated

Transparent

No

Dimensions

Height

75 mm

Width

75 mm

Depth

52.30 mm

Installation, mounting

Mounting on

Surface mounting

Controls and indicators

Number of buttons

1

Type of push button

Single push button

With feedback signal contact

No

Safety

Ingress Protection (IP) class

IP44

Accessories

Has labelling field

No

Texts

Installation mode

For screw fastening

Lighting

Can be illuminated using neon and glow lamp unit with N-terminal
For lighting and monitoring circuit

Terminal

Wago clip-in 3-wire connection terminal for wiring

Type of connection

With plug-in terminals