



Push-button, NO contact 2 sep. signal contacts surf.-mtd, Iso Panzer IP44, gr/ye

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Grey
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated
Transparent	No

Dimensions

Height	75 mm
Width	75 mm
Depth	56 mm

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	Yes

Safety

Ingress Protection (IP) class	IP44
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Texts

Imprint	Without imprint
Installation mode	For screw fastening
Lighting	Can be illuminated with neon and glow lamp unit With neon lamp unit for rocker switch and rocker push-button order no. 1615 For lighting and monitoring circuit
Type of connection	With plug-in terminals