



383800



Group spring-return push-B 2p,isolated input term.,neut. poS,1930/glass/R.cl

Technical Features

Electric current	
Momentary contact current	10 A
Voltage	
Rated voltage	250 V
Architecture	
Control/operation element	Short rotary handle
Number of poles	2
Materials	
Material	Metal Plastic
Treatment	Untreated
Transparent	No
Dimensions	
Height	71 mm
Width	42 mm
Depth	42 mm
Built-in depth	32 mm
Installation, mounting	
Mounting on	Flush mounting
Controls and indicators	
Number of buttons	0
Type of push button	Group push button
With feedback signal contact	No
Safety	
Ingress Protection (IP) class	IP20
Accessories	
Has labelling field	No
Texts	
Imprint	Without imprint
Installation mode	With spreader claws
Switch mode	With neutral position
Type of connection	With screw terminals