




JPD3012M16DX1

DB, apex+, 30/12Pole, 160A MCCB Twin, 8 Modules, orange, 1200x600x200mm

Technical Features

Connection

Number of accessible phases	42
-----------------------------	----

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	160 A
Breaking and opening capacity Idm	0 kA

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Split chassis

Capacity

Number of modules	42
-------------------	----

Weight

Weight	59 kg
--------	-------

Dimensions

Height	1200 mm
Width	600 mm
Depth	200 mm

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Steel
Colour	Orange

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP43
Locking type	3-point lever Key lock

Architecture

Number of poles	42
-----------------	----

Sustainability

RoHS conform	Yes
--------------	-----