



JPD1812S25DX1

DB, apex+, 18/12Pole, 250A Isolator Twin,8 Modules,orange,1200x600x200mm

### Technical Features

#### Connection

|                             |    |
|-----------------------------|----|
| Number of accessible phases | 30 |
|-----------------------------|----|

#### Installation, mounting

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

#### Electric current

|                                   |       |
|-----------------------------------|-------|
| Rated current                     | 250 A |
| Breaking and opening capacity Idm | 0 kA  |

#### Equipment

|                        |               |
|------------------------|---------------|
| With lock              | Yes           |
| Has mounting plate     | No            |
| Equipped with switch   | No switch     |
| Number of switches     | 0             |
| Type of busbar chassis | Split chassis |

#### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 42 |
|-------------------|----|

#### Dimensions

|        |         |
|--------|---------|
| Height | 1200 mm |
| Width  | 600 mm  |
| Depth  | 200 mm  |

#### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

#### Materials

|          |        |
|----------|--------|
| Material | Steel  |
| Colour   | Orange |

#### Safety

|                               |                           |
|-------------------------------|---------------------------|
| Protection class              | Isolation class I         |
| Impact resistance IK          | IK05                      |
| Ingress Protection (IP) class | IP43                      |
| Locking type                  | 3-point lever<br>Key lock |

#### Architecture

|                 |    |
|-----------------|----|
| Number of poles | 30 |
|-----------------|----|