



JPD4818M16DX1

DB, apex+, 48/18Pole,160A MCCB Twin, 8 Modules, orange, 1400x600x200mm

Technical Features

Connection

Number of accessible phases 66

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 160 A

Breaking and opening capacity I_{dm} 0 kA

Equipment

With lock Yes

Has mounting plate No

Equipped with switch No switch

Number of switches 0

Type of busbar chassis Split chassis

Capacity

Number of modules 42

Weight

Weight 64 kg

Dimensions

Height 1400 mm

Width 600 mm

Depth 200 mm

Cover, door

Door/cover is transparent No

Materials

Material Steel

Colour Orange

Safety

Protection class Isolation class I

Impact resistance IK IK05

Ingress Protection (IP) class IP43

Locking type 3-point lever
Key lock

Architecture

Number of poles 72

Sustainability

RoHS conform Yes