# Product Datasheet
JPE9600S25DX



JPE9600S25DX1

**DB, elite, 96Pole,250A Isolator 2x8 Mod+26 Mod,orange,1600x600x250mm**

## Technical Features

| | |
|---|---|
| **Connection** | |
| Number of accessible phases | 96 |
| **Installation, mounting** | |
| Mounting on | Surface mounting |
| **Electric current** | |
| Rated current | 250 A |
| **Equipment** | |
| With lock | Yes |
| Has mounting plate | No |
| Equipped with switch | Isolator |
| Number of switches | 1 |
| Type of busbar chassis | Fixed load chassis |
| **Capacity** | |
| Number of modules | 42 |
| **Weight** | |
| Weight | 73 kg |
| **Dimensions** | |
| Height | 1600 mm |
| Width | 600 mm |
| Depth | 250 mm |
| **Cover, door** | |
| Door/cover is transparent | No |
| **Materials** | |
| Material | Steel |
| Colour | Orange |
| **Safety** | |
| Protection class | Isolation class I |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP66 |
| Locking type | 3-point lever<br>Key lock |
| **Architecture** | |
| Number of poles | 96 |
| **Sustainability** | |
| RoHS conform | Yes |