# Product Datasheet
JPE3618M16DX



JPE3618M16DX1

**DB, elite, 36/18Pole,160A MCCB Twin, 8 Modules, orange, 1400x600x250mm**

## Technical Features

| | |
|---|---|
| **Connection** | |
| Number of accessible phases | 54 |
| **Installation, mounting** | |
| Mounting on | Surface mounting |
| **Electric current** | |
| Rated current | 160 A |
| **Equipment** | |
| With lock | Yes |
| Has mounting plate | No |
| Equipped with switch | MCCB |
| Number of switches | 1 |
| Type of busbar chassis | Split chassis |
| **Capacity** | |
| Number of modules | 42 |
| **Weight** | |
| Weight | 67 kg |
| **Dimensions** | |
| Height | 1400 mm |
| Width | 600 mm |
| Depth | 250 mm |
| **Cover, door** | |
| Door/cover is transparent | No |
| **Materials** | |
| Material | Steel |
| Colour | Orange |
| **Safety** | |
| Protection class | Isolation class I |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP66 |
| Locking type | 3-point lever<br>Key lock |
| **Architecture** | |
| Number of poles | 54 |